

## AMPTEC 620MC DATASHEET



The AMPTEC 620MC meter contains ranges from 20Ω to 2.0 MΩ. It is compatible with all of our 620-SERIES options, including our OP-232 RS232C Interface, OP-247 Optically Isolated Operating Power, and OP-519 Rack Mount Tray.

AMPTEC 620MC IGNITER TESTER SPECIFICATIONS					
<b>RANGE</b>	20 Ω	200 Ω	2 KΩ	200 KΩ	20 MΩ
<b>NOMINAL CURRENT</b>	5 mA	.5 mA	50 uA	0.5 uA	.010 uA
<b>FAILSAFE CURRENT</b>	8 mA	1.5 mA	150 uA	1.5 uA	.015 uA
<b>RESOLUTION</b>	1 mΩ	10 mΩ	100 mΩ	10 Ω	1 KΩ
<b>ACCURACY</b>	± .02% of reading & range	± .02% of reading & range	± .02% of reading & range	±.05% of reading & range	± 2% of reading, ± 0.2% of range

AMPTEC 620MC IGNITER TESTER GENERAL SPECIFICATIONS					
<b>TERMINAL</b>	4-Wire Kelvin	<b>WEIGHT</b>	3 lbs.	<b>OPERATING TEMP.</b>	0° to 50° C
<b>DISPLAY</b>	4 ½ digit LED	<b>SIZE</b>	9.75" x 10" x 3.25"	<b>STORAGE TEMP.</b>	-10° ± 70° C
<b>UPDATE</b>	3 readings per second	<b>MAX. INTERNAL VOLTAGE</b>	4.8 VDC	<b>TEMP. COEFFICIENT</b>	± .002% per 15° C
<b>POWER</b>	Rechargeable, 4ea NICAD batteries (5 AHr)	<b>OPEN CIRCUIT</b>	1.6 VDC	<b>MAX. INPUT VOLTAGE</b>	250 VDC

AMPTEC 620MC IGNITER TESTER ORDERING INFORMATION	
MODEL/SKU #	DESCRIPTION
<b>620MC</b>	Failsafe Ohmmeter, OP-300 Leads, N.I.S.T. Calibration Certificate, 620-DC Battery charger
<b>OP-100</b>	Meter transit/hard shell case
<b>OP-110</b>	Test lead storage pouch
<b>OP-232</b>	Optically isolated RS232C Interface
<b>OP-247</b>	Continuous Isolated power
<b>OP-290</b>	Alligator clip test lead set
<b>OP-300</b>	Gold plated 4-Wire Kelvin clip leads
<b>OP-302</b>	5-way banana jack backed Kelvin clips
<b>OP-401</b>	Gold plated single tip Kelvin probes
<b>OP-403</b>	Standard handheld Kelvin mini-probes
<b>OP-519S</b>	Single rack mount tray
<b>620-BAT</b>	Set of replacement/extra 4 NICAD D-cell batteries
<b>620-DC</b>	Battery charger for 620 SERIES products

For customized products, or probe/lead sets, contact our sales department. The above is not a complete list – we offer many more varieties of accessories and probe/lead sets.



**AMPTEC RESEARCH**  
 T: (512) 858-4045 E: info@amptec.com  
 13231 Rooster Springs Rd., Austin, TX 78737  
[www.amptec.com](http://www.amptec.com)